320A

OPTICAL RETURN LOSS TEST SET

BRT-320A

NETWORK TESTING



Fast Stabilization

EXFO's BRT-320A is a field-ready return loss test set offered in five configurations: 1310 nm, 1550 nm or 1625 nm; dual-wavelength 1310/1550 nm or 1550/1625 nm. All come equipped with rapidly stabilizing TEC lasers and low-drift photodetectors to ensure constant optical return loss (ORL) measurements year after year.

Built-In User-Friendliness

Use the BRT-320A to read backreflection from 0 dB to -70 dB and easily store up to 300 readings in a non-volatile memory. ORL readings appear directly on the large, backlit LCD. An ORL zero function accounts for incidental backreflections before the point of measurement and complies with Bellcore optical continuous wave reflectometer (OCWR) requirements. In User Calibration mode, you can calibrate the unit to a known reflection. Other features include three-way powering (rechargeable NiCd battery pack, 9 V battery, AC adapter/charger), 0.01 dB resolution, \pm 0.1 dB linearity, internal InGaAs detector, low-battery indicator and a protective holster with shoulder strap.

Reveal Return Loss Problems

Many digital and analog fiber systems require ORL characterization. ORL along a fiber span is a combination of Rayleigh scattering and Fresnel reflections. Together, these phenomena can reduce fiber system performance and increase bit error rate (BER) by degrading transmitter stability. The BRT-320A measures cumulative link return loss and individual component reflectance to reveal potential ORL problems before they seriously affect your applications.

Versatile

The BRT-320A is ideal for local and long-distance Telco, CATV, utility, broadband and transmission equipment manufacturing applications. These environments often require complete network ORL characterization and component reflectance verification. The BRT-320A also functions as a stable, continuous-wavelength light source for attenuation measurements. Other applications include fiber component and cable manufacturing.





Model		BRT-320A-02BLC-58	BRT-320A-03BLC-58	BRT-320A-23BLC-58	BRT-320A-04BLC	BRT-320A-34BLC		
Wavelength (nm)		1310 ± 15	1550 ± 15	1310/1550 ± 15	1625 ± 15	1550/1625 ± 15		
Spectral width (rms) ² (nm)		< 5	< 5	< 5	< 5	< 5		
Output power stability (dB) 15 minutes ³		± 0.01	± 0.01	± 0.02	-	-		
1 hour⁴		± 0.05	± 0.05	± 0.06	-	-		
Temperature stability⁵ (dB)		± 0.2	± 0.2	± 0.3	-	-		
Reflection range (dB)		0 to -70	0 to -70	0 to -70	0 to -70	0 to -70		
Display resolution ⁶ (dB)		0.01	0.01	0.01	0.01	0.01		
Linearity ⁷ (dB)		± 0.1	± 0.1	± 0.1	± 0.1	± 0.1		
Uncertainty (accuracy)7 (dB) ± 0.5		± 0.5	± 0.5	± 0.5	± 0.5			
Minimum output power (dBm)		-6.5	-6.5	-7.5	-3	-9/-7		
Polarization sensitivity ^s (dB)		± 0.15	± 0.15	± 0.15	± 0.15	± 0.15		
GENERAL SPECIFICA	TIONS1							
Size (H x W x D)		21 cm x 11 cm x 5 cm	(8 3/4 in x 4 1/2 in x 2 in)					
Weight	unit	0.8 kg	(1 ³ / ₄ lb)					
	shipping	2.5 kg	(5 ¹ / ₂ lb)					
Temperature	operating	-10 °C to 40 °C	(14 °F to 104 °F)					
	storage	−30 °C to 60 °C	(-22 °F to 140 °F)					
Relative humidity		0 % to 95 % non-condensing	0 % to 95 % non-condensing					
Power		Built-in NiCd batteries (10 hours	Built-in NiCd batteries (10 hours of operation), 9 V alkaline battery backup, AC adapter/charger					

ORDERING INFORMATION

BRT-320A-XXBLC-XX

Source code

02BLC = 1310 nm TEC laser

03BLC = 1550 nm TEC laser

23BLC = 1310/1550 nm TEC laser

04BLC = 1625 nm TEC laser

34BLC = 1550/1625 TEC nm laser

Connector code -

EA-EUI-28 = APC/DIN 47256

EA-EUI-89 = APC/FC narrow key

EA-EUI-91 = APC/SCEA-EUI-95 = APC/E-2000

With EA, a standard test jumper is provided:

EUI-28 = TJ-B86-86

EUI-89 = TJ-B58-58

EUI-91 = TJ-B88-88

EUI-95 = TJ-B96-96

STANDARD ACCESSORIES

User Guide, AC adapter/charger, NiCd batteries, 9 V alkaline battery, carrying case, protective holster, shoulder strap, mandrel tool, complimentary test jumper, and Certificate of Compliance.

SAFETY

This product complies with 21 CFR 1040.10 and IEC 60825-1:Ed 1.1 1998:

CLASS 1 LASER PRODUCT

- 1. Characterized at 23 °C ± 2 °C (70 °F ± to 77 °F).
- 2. rms = root mean square.
- 3. Typical, after 5-minute warmup (measurement mode activated only after warmup).
- Typical, after a 15 minute warmup.
- 5. For temperatures ranging from -10 °C to 40 °C (14 °F to 104 °F).
- 6. From 0 dB to -30 dB.
- 7. For reflection measurements from -15 dB to -50 dB. Connector on measurement port must cause less than -50 dB of reflection to maintain resolution.
- 8. Typical.

Example: BRT-320A-02BLC-EA-EUI-89

Find out more about EXFO's extensive line of high-performance portable instruments by visiting our website at www.exfo.com.



OLTS

-Power meter

Light source Talk set



Optical Fiber

OTDR

OLTS

-Switch

DWDM Test Systems

- Multiwavelength meter

-OSA

-PMD analyzer ORL meter - Chromatic dispersion analyzer

Telecom/Datacom

-10/100 and Gigabit Ethernet -SONET/SDH (DS0 to OC-192c)

-SDH/PDH (64 kb/s to STM-64c)

Corporate Headquarters > 400 Godin Avenue, Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 | Fax: 1 418 683-2170 | info@exfo.com

		Toll-	-free: 1 800 663-3936 (USA	and Canada) www.exfo.com
EXFO America	4275 Kellway Circle, Suite 122	Addison, TX 75001 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164
EXFO Europe	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85	Fax: +33.1.40.83.04.42
EXFO Asia-Pacific	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242
EXFO China	Beijing New Century Hotel Office Tower Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662
	No. 6 Southern Capital Gym Road			

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at http://www.exfo.com/specs In case of discrepancy, the Web version takes precedence over any printed literature







