# Megger.

# BITE2 and BITE2P Battery Impedance Test Equipment



- Determines condition of lead-acid and NiCd cells up to 7000 Ah
- On-board Pass/Warning/Fail indications
- Robust, repeatable instruments
- On-line testing
- Checks charger condition by measuring ac ripple current
- Includes PowerDB LITE Software

# DESCRIPTION

The BITE2 and BITE2P Battery Impedance Test Equipment determine the condition of lead-acid and nickel-cadmium cells up to 7000 Ah. An advanced feature set has been developed that includes Pass/Warning/Fail calculations based on a userentered baseline value, advanced printing functions and more. The case of the BITE2P consists of both the transmitter and a carrying case for all of the standard accessories and some of the optional accessories, in an all-in-one unit. The BITE2 and its accessories fit into a sturdy canvas case with a shoulder strap.

The instruments work by applying a test signal across the battery string while on-line, then calculates impedance based on simultaneous measurements of current and resulting voltage drop of each cell/jar. They also measure dc voltage and interconnection (strap) resistance to help determine the overall condition of the entire battery string's electrical path from terminal plate to terminal plate.

In addition, the BITE2 and BITE2P measure ac ripple current which, if too high and over an extended period of time, can damage the battery by heating it. (An increase of battery temperature by 18°F/10°C will halve the life of lead-acid batteries.) Battery manufacturers generally recommend a limit of 5A of ac ripple current for every 100 Ah of battery capacity. The first measurement that the instruments take is ac ripple current which should be trended.

The BITE2 and BITE2P receiver stores the readings in its internal memory. These measurements, along with other maintenance data such as ambient and pilot cell temperatures and ac ripple current, assist in determining the overall condition of battery systems. Megger recommends that impedance measurements with the

BITE2 or BITE2P be made part of a battery maintenance program with readings taken and recorded semiannually for flooded batteries and quarterly for VRLA.

Unlike load cycle testing that involves substantial downtime and repeated discharges, using the instruments require no battery discharge, nor do they stress the battery in any way compared to other techniques. With a test time of less than 15 seconds for each cell and intercell connector, one person can easily, quickly, and precisely measure internal cell impedance, dc terminal voltage and intercell connection resistance without taking the battery system off line and evaluate charger condition also.

Naturally, everything you need to perform these tests is included with the basic instruments. There is a full line of optional accessories to enhance the capabilities of the BITE2 and BITE2P. Both have the ability to download to a PC for data interpretation and to PowerDB, Megger's battery database management software. Additionally, the BITE2P has a built-in printer to review the active test and also to leave a hard copy record at the site.

# Receiver

The battery-operated receiver incorporates the potential leads, clamp-on current sensor, and data storage capabilities. It stores more than 2000 sets of data (cell impedance, cell voltage and interconnecting strap resistance, date and time stamps) in up to 300 tests. It also allows for printing the active test for easy review and retest. Selective printing of any test and deleting oldest tests are now included features to maintain in memory the most critical tests.

At any time while performing a test, the operator can review the current test results by using arrow keys and scrolling back through the active test screen. The operator can also print the active test using the BITE2P transmitter printer. If needed, the operator can retest any of the cells and straps in the current test. Stored data can also be downloaded via the RS-232 connector directly to a personal computer or the BITE2P transmitter printer.

One additional feature of the receiver is that if you are called away while in the middle of the test, simply shut down the instrument and it will remember where you left off in the test.

The clamp-on current sensor is connected to the receiver during testing and clamped around a convenient intertier or intercell connection within the loop created by the transmitter's current source leads and the battery string. If the intercell or intertier connection consists of more cables than the diameter of the



# BITE2 and BITE2P Battery Impedance Test Equipment

clamp-on current sensor can encompass, the receiver has a splitstrap function.

There are optional RopeCTs<sup>™</sup> available for large buss work. With the optional bar-code wand, additional information such as location ID, user ID, ambient and pilot cell temperatures can be recorded and stored. There is space on the printout to enter specific gravity readings.

	Ba	ttery	Analy	sis Repor	t				
Location ID									
User ID:									
Notes:									
Ambient Te			Pilo	t Temp:					
		1Δ	A Test AC Current: 9.8 A						
			V/F: 11.00 mW/20%/40%						
marapher.	1 0/	••/1.		0 11100/20	/0/40 /0				
	05-SEP-2000								
Cell Sp.G	r. ZbmW	/ P/W	//F %	RS mW	Volts DC	Time			
001	12.09	Р	09	0.412	13.52	11:13			
002	12.22		11		13.34	11:14			
003	14.02			0.405	13.59				
004	14.54		32	0.403					
005	12.60		14	0.042	13.27				
006	12.09	Р	09	0.405	13.38	11:17			
	Cel	l Impe	danc	e Summa	rv				
		Ā	Average		Maximum				
12.09			12.93		14.54				
	Percen	t Devi	ation	from Ave	arage				
	-1		0	10	20 30				
001	_		-						
002									
003									
004									
005		1							
006									

Figure 1. Sample battery analysis report

# Transmitter

The transmitter provides the capacitively coupled ac test signal to avoid transients on the dc buss and applies it to the cells under test via the source leads. Both the BITE2 and BITE2P transmitters have an LCD and built-in receiver charger, while the BITE2P transmitter features a built-in printer.

Data, measured and stored in the receiver can be exported to a PC. It can also be printed to the BITE2P transmitter printer where it can be reviewed. Figure 1 shows a sample printout of a full battery analysis report.

# **APPLICATIONS**

A battery's internal impedance increases with decreasing capacity due to various conditions such as age, ambient temperature, discharge history, etc. See Figure 2. Both the BITE2 and BITE2P measure impedance values and dc voltage for leadacid and nickel-cadmium cells up to 7000 Ah capacity.

Impedance finds electrical path problems due to plate sulphation, post-seal corrosion, dry-out, and poor intracell and intercell connections. This information lets the operator determine maintenance needs such as:

- Cell replacement criteria based on impedance trends.
- Jumpering out a cell or two.
- Clean and/or retorque intercell connectors.
- Shorten the maintenance interval, etc.

Typical installations that can be tested using the BITE2 and BITE2P include:

- Electrical power generation plants.
- Substations: utility, railroad, industrial

# Telecommunications facilities: CO, Wireline, Wireless, MTSO

- UPS systems
- Railroad: Signals and Communications, substation
- Aircraft power supplies
- Marine, military

#### FEATURES AND BENEFITS

- On-line testing requiring no downtime.
- Enhanced printing and memory functions.
- Calculates impedance automatically and stores results for on-site review.
- Requires no battery discharge.
- Receiver can download stored data to PowerDB software for quick, easy analysis.
- Reduced test time: less than 3 seconds for each cell.
- Measures impedance and dc voltage values for all lead-acid and nickel-cadmium cells up to 7000 Ah.
- Stores more than 2000 sets of readings in up to 300 tests.
- Checks charger condition by measuring ac ripple current.
- PowerDB LITE allows data to be stored and allows custom reporting. (ideal for NERC & FERC requirements)

## **Test Procedure**

The BITE2 and BITE2P work by applying a capacitively coupled ac test signal across the battery string while on-line. The receiver and potential probe are placed at the cell terminals to measure the signal and resulting voltage drop for each cell/jar. During each measurement, impedance is calculated following Ohm's Law, displayed on the LCD and stored. The instruments also measure, display and record dc voltage and interconnection (strap) resistance to help determine the overall condition of the entire battery string's electrical path from terminal plate to terminal plate. The also measure ac ripple current, a charger parameter.

The BITE2 and BITE2P receiver stores the readings in its internal memory. These measurements, along with other maintenance data such as ambient and pilot cell temperatures and ac ripple current, assist in determining the overall condition of battery systems. Figure 2 shows a typical test setup.

# **Interpretation of Readings**

Data produced by the BITE2 and BITE2P can be interpreted in several modes: instantaneous, short-term and long-term time frames. PowerDB makes data analysis fast & easy. See figure 3.




Figure 2. A typical test setup

# Megger.

www.megger.com		Megger.	Megger,	BATTERY TEST	Megger
SURSTATION	HAZELTON POSITION	TEST PAGE	12		PAGE
	1	DATE 5/6/2009	Avg. Shap Resistance 0.070		
DI TRES	AMBIENT TEMPERATURE 25 10	NUMDHY 5. 2084	STRAP # RESISTANCE IN WARATION (Aug)	TIME CONNECTED TO THE	
	BITE3	TESTED BY Darryl Evans	3 0.077 10 4 0.073 42	08.45 3 Inter-cell 08.43 4 Inter-cell	
ITRING NAME INSTALLATION DATE KUMBER OF CELLS: 12 CHANGER MANUFACTURER MODEL		12 80 VRC   EQUALIZATION VOLTAGE VOIS   CURRENT Areys VOLTAGE Vois	8 0.991 4.9   4 0.10 0.11   7 0.67 4.1   8 0.27 0.1   10 0.01 0.1   10 0.02 0.01   11 0.06 5.5   12 120 0.00   12 0.00 0.00	(9.4) 5. Hele-(el)   98.4) 6. Hele-(el)   98.4) 7. Hele-(el)   98.40 8. Hele-(el)   98.40 8. Hele-(el)   98.40 9. Hele-(el)   98.40 9. Hele-(el)   98.50 9. Hele-(el)   98.50 10. Hele-(el)   98.50 11. Hele-(el)   98.50 12. Hele-(el)	
MITS: LOW VOLTAGE LIMIT (V): 1	RPPLE CURRENT	FLOAT CURRENT	192.00 192.00 192.00		
		1	BORTED IMPEDANCE WHILATION ORAFH	Citizer -	
Basevo repederar S + NOTS -	MULE CEVATOR IS INVOLVED CENAZO   1000 0000 0001 0001   3444 548 448 448   3444 548 458 550   3444 548 550 500   3190 610 610 610   3190 610 610 610   4465 207 610 610   259 139 620 610   4465 207 610 620   300 37 620 600	No. Yology 1 (f) No. Yology 2 (f) Oct. S (f)   Yold OCL. (f) OCL. (f) OCL. (f)   Yold OCL. (f) OCL. (f) OCL. (f) OCL. (f)   Yold OCL. (f) OCL. (f) OCL. (f) OCL. (f) OCL. (f)   Yold OCL. (f) OCL. (f) OCL. (f) OCL. (f) OCL. (f) OCL. (f)   Yold OCL. (f) OCL. (			
Ang Sinap Resistance 0.076 STRAP # (NESISTANCE In VAR onti-christ) (A	TANTON MEADURINGMENT CRLL   logi TAKE DOAMECTED TO TYPE   00.49 T MIR-det MIR-det   00.49 2 MIR-det MIR-det			Col Runder	
CONVERSE & SANS-ING PARTICI	1, 18C, www.power@r.com	10750, ###1580 2/5/2010	COPYRIGHT & 2002-2008 POMMEND, DEC.	www.powerdb.com	10750, MEVICED 2/5/20



# Instantaneous Interpretation


The operator can enter a baseline value from either the impedance measurements obtained at commissioning. The percent changes from baseline for warning and fail levels are entered, but 20 percent and 40 percent are the default settings. The LCD on the receiver will display the status of the cell for a few seconds before proceeding to the next cell. The status of each cell/jar will be printed on the Battery Analysis Report.

## **Short-Term Interpretation**

Impedance readings for individual cells can be used in the short term to compare with the average impedance readings for the entire battery string. Individual cell values with deviations of more than  $\pm 15\%$  for flooded lead-acid,  $\pm 35\%$  for VRLA, and 50% for NiCd cells from the battery string average typically indicate a problem with that cell. Megger recommends additional investigation of such cells including a verification of intercell connections and a single cell load-cycle test.

#### **Long-Term Interpretation**

Impedance readings for the entire battery can be used in the long term to determine replacement criteria. Battery cell impedance values should be recorded and compared to previous readings to determine the position of the cell on the curve of impedance versus cell life as shown in Figure 4. Based on experience, a variation of  $\pm 20\%$  from baseline for flooded leadacid,  $\pm 40\%$  for VRLA and 50% for NiCd cells indicate significant change in the electrical path to warrant serious evaluation of the condition of the battery system. Megger maintains a database of impedance values by some manufacturers and battery size/type. For comparison purposes, this information is available upon request.





# **SPECIFICATIONS**

#### Application

The BITE2 and BITE2P test lead-acid and nickel-cadmium cells up to 7000 Ah.

## **Maximum Total Voltage at Current Source Leads**

275~V dc (larger battery systems can be sectioned to accommodate this specification)

## Transmitter

Supply Voltage

100 to 130 V, 50/60 Hz, 200 VA max 210 to 250 V, 50/60 Hz, 200 VA max

## **Source Output Current**

10 A nominal, 50/60 Hz operation

#### Maximum Battery String Test Voltage

275 V dc at source lead terminals (section the battery if >275 Vdc)

**Display** Digital LCD meter, 0 to 15 A

#### **BITE2P Printer**

Built-in thermal, with 4.25 in. (110 mm) printing width

# Megger

# Charger

Supply Voltage 100 to 130 V, 50/60 Hz, 14 VA 210 to 250 V, 50/60 Hz, 14 VA

Output 6.50 V dc @ 1.10 A dc charging (max) 9.60 V dc open circuit

## Receiver

Accuracy

ac impedance 5% +1 LSD dc voltage  $\pm(1.5\% \text{ of } rdg + 1 \text{ LSD})$ 

Precision Better than 0.5% one sigma

#### Voltage Range and Resolution

1 to 2.500 V dc, 1 mV resolution 2.5 to 25.00 V dc, 10 mV resolution

#### Impedance Range and Resolution

0 to 1.000 m $\Omega$ , 1µ $\Omega$  resolution 1 to 10.00 m $\Omega$ , 10µ $\Omega$  resolution 10 to 100.0 m $\Omega$ , 0.1m $\Omega$  resolution

#### Settling Time per Reading

3 seconds maximum

Display LCD, 2 x 16 characters

# Supply

4.8 V dc, 800 mAh, guick charge NiMH battery pack

**Battery Pack Life, Full Charge** 5 hours continuous

# Maximum Cell/Jar Test Voltage

25 V dc between receiver and potential probe

# **BITE2 and BITE2P Battery Impedance Test Equipment**

#### Temperature

**Operating:** 32 to 105° F (0 to 40° C) **Storage:** -5 to 130° F (-20 to 55° C) Humidity: 20 to 90% RH, noncondensing

#### **Clamp Range** Standard CT 2.0 in. (50 mm) maximum opening

**Optional Miniature CT** 0.5 in. (12 mm) maximum opening

**Optional RopeCT**<sup>™</sup> 6 in. (150 mm) opening, approx.

**Standards** Conforms to the EMC Directive 2004/108/EC and the LVD Directive 2006/95/EC

## Dimensions

Transmitter BITE2: 6.5 H x 14 W x 10.6 D in. (16.5 H x 35.6 W x 27 D cm) **BITE2P:** 7.5 H x 18.5 W x 14.6 D in. (19 H x 47 W x 37 D cm)

**Receiver (irregular shape)** 7.25 H x 11.25 W x 2 D in. (18 H x 29 W x 5 D cm)

# Weight

Transmitter BITE2: 17 lb (7.7 kg) BITE2P: 18 lb (8.2 kg) alone, 32 lb (14.5 kg) packed

Receiver 1.6 lb (0.7 kg)

	ORDERING INFORMATION			
Item (Qty)	Cat. No.	ltem (Qty)		
BITE2, 110/230 V ac, 50/60 Hz	246002B	Manual for BITE2 and BITE2P		
BITE2P, 110/230 V ac, 50/60 Hz	246004	Accessory bag for BITE2		
Included Accessories		<b>Optional Accessories</b>		
Transmitter for BITE2	P30044-300	Current sensor 0.5 in. (12 mm) oper		
Transmitter for BITE2P	P30044-100	with 2.5 ft (0.8 m) lead		
Receiver	P30620-3	CT extension cable, 20 ft (6 m)		
Fused Source Leads, 20 ft (6 m)	29386-4	Current source leads, 10 ft (3 m), fuse		
Current sensor, 2 in. (50 mm) opening		Current source leads, 30 ft (9.1 m), fu		
with 5 ft (1.5 m) lead	2002-786	Current source leads, 40 ft (12.2 m), f		
CT extension cable, 20 ft (6 m)	33864-2	Bar code scanner kit with preprinted		
Communication cable, 6 ft (1.8 m)	35340	Flex Current Clamp (6" ID)		
Charger cable	35341			
Thermal paper	26999			
ac line cord, 8 ft (2.5 m)	17032-7			

# 29996 ening 246034 33864-2 ed 246147 246347 used fused 246447 d code sheet 246201 MCCA-100B2

# SALES OFFICE

Megger USA -Valley Forge Corporate Center 2621 Van Buren Avenue, Norristown, Pennsylvania, 19403, USA T. 1-610 676 8500 F. 1-610-676-8610

## BITE2 2P DS en V25

www.megger.com **ISO 9001** The word 'Megger' is a registered trademark

# Megger

Cat. No. AVTM246004